


Datasheet

Bin Urano with lid and ashtray

Product code 331

Rev. 0 of 10/06/2016



Dimcar si riserva di apportare, in qualsiasi momento, modifiche sui prodotti ritenute utili al miglioramento qualitativo degli stessi; le immagini contenute nelle schede potrebbero non riprodurre fedelmente i colori reali degli articoli.

Datasheet

Bin Urano with lid and ashtray

Product code 331

Rev. 0 of 10/06/2016



DESCRIPTION

Structure

The Urano waste bin with lid and ashtray is made up of a support upright in round tubular galvanized steel Ø mm. 76x2, adorned in the upper part with a decorative frieze; in the lower part the upright is equipped with a hole-covering flange in galvanized steel.

- Shaped lid in galvanized steel sheet thickness mm. 3, reinforcement bezel, in the upper part, obtained from high definition plasma cutting, and made of galvanized sheet.
- Fixed circular ashtray, incorporated in the center of the lid, complete with a micro-perforated plate for extinguishing cigarettes; the semi-circular plate is made of polished AISI 304 stainless steel sheet thickness mm.
- Shaped lower arm for supporting the basket in galvanized steel sheet.
- Basket, cylindrical in shape, made of galvanized sheet thickness mm. 1 with 3 full areas and 2 areas characterized by circular holes arranged in sequential diamonds; upper part with anti-cut edge and bag-holding ring made of solid round galvanized steel, hinged to the edge of the basket.
- Shaped bottom in 1.5 mm thick galvanized steel sheet with holes for draining rainwater.

Overall weight: 10Kg

Datasheet

Bin Urano with lid and ashtray

Product code 331

Rev. 0 of 10/06/2016



FINISH ACCORDING TO THE CATALOGUE



Gun metal gray
(Steel parts)

Customers can request a different finish from the RAL color options available on our website.

PRODUCT OPTIONALS



Product code 237-M - Cicco ashtray with wall mounting

Datasheet

Bin Urano with lid and ashtray

Product code 331

Rev. 0 of 10/06/2016



TREATMENTS AND FINISHES THAT PREVENT CORROSION

Washing

Spray treatment is used to get rid of oils and fats from metal surfaces by using special degreasing liquids. The process involves drying in a dryer for 15 minutes.

Sandblasting

The porosity of metal surfaces is increased by the manual sandblasting process with river sand, which results in an increase in thermosetting powder adhesion.

Anticorrosive application

The first step in the coating process involves using a thermosetting powder anti-corrosion base made of epoxy resins and specific pigments. It provides enough protection against the elements.

Anticorrosive polymerization

The process involves cooking in an industrial curing oven at 180°C. In this step, the powder is transformed into a coating that is uniform, smooth, and lasting.

Polymerization coloured finish

The final phase of coating with thermosetting powders. The application complies with the same principles as the anti-corrosion.

Polymerization colored finish

The final product will be cured in an industrial curing oven at a temperature of 180°C. The procedure is based on the same principles as the polymerization of the anti-corrosion agent. The powder becomes a uniform coating, and the surface becomes the characteristics of the chosen color type, including smooth, peeled, or wrinkled, etc.

3/5

Dimcar si riserva di apportare, in qualsiasi momento, modifiche sui prodotti ritenute utili al miglioramento qualitativo degli stessi; le immagini contenute nelle schede potrebbero non riprodurre fedelmente i colori reali degli articoli.

Datasheet

Bin Urano with lid and ashtray

Product code 331

Rev. 0 of 10/06/2016



DELIVERY

Prodotto fornito in kit di assemblaggio con viteria in acciaio ed istruzioni per il montaggio e fissaggio.

FIXING

Il prodotto deve essere installato mediante cementazione.

CORPORATE CERTIFICATES

ISO 9001:2015

Quality Management System.

UNI EN ISO 3834-3:2021

Welding quality management system.

Processing center

Certificate according to Italian Law D.M. of 17 Jan 2018